



TRACK PROFILE DETAILS AND SUPPORT CENTERS REQUIREMENTS

Track Series	Track Description	Track Height (Inches)	Weight Per Foot (Pounds)	MAXIMUM SUPPORT CENTERS (Feet/Inches)				MAXIMUM OVERHANG (Feet/Inches)			
				1 Person	2 Person	3 Person	4 Person	1 Person	2 Person	3 Person	4 Person
PT500	Plain Single Track	2-3/8"	3.8	10'	8'	6' 6"	5' 4"	2'	1' 7"	1' 4"	1' 1"
PT600		2-15/16"	5.9	15'	12' 6"	10'	8'	3'	2' 6"	2'	1' 7"
*PT700		4-5/16"	11.1	18'	15'	13'	12'	3' 7"	3'	2' 7"	2'
**PT500SS	Stainless Steel Plain Single Track	2-3/8"	3.8	7'	5' 6"	4' 6"	3' 8"	1' 5"	1' 1"	11"	9"
R520	Trussed Single Track	10"	10.1	20'	17'	14'	11' 6"	4'	3' 5"	2' 10"	2'
R525		12-3/8"	10.5	25'	18'	15'	12'	5'	3' 7"	3'	2' 5"
R530		14-3/8"	12.9	30'	25'	21'	17'	6'	5'	4' 2"	3' 5"
R620	Trussed Single Track	11"	14.2	33'	28'	23'	19'	6' 7"	5' 7"	4' 7"	3' 10"
R625		13-7/8"	14.8	36'	31'	25'	21'	7' 2"	6' 2"	5'	4' 2"
R630		17"	17.5	49'	42'	35'	28'	9' 10"	8' 5"	7'	5' 7"
R520C	Capped Trussed Single Track	10-1/4"	18.5	40'	33'	27'	22'	4'	3' 5"	2' 10"	2'
R525C		12-5/8"	18.9	50'	42'	35'	28'	5'	3' 7"	3'	2' 5"
R530C		14-5/8"	21.3	58'	48'	40'	32'	6'	5'	4' 2"	3' 5"
520DST	Trussed Dual Track	10"	13.9	N/A	38'	32'	29'	N/A	5'	4'	3'
525DST		12-3/8"	14.3	N/A	45'	39'	32'	N/A	6'	5'	4'
530DST		14-3/8"	16.7	N/A	53'	45'	36'	N/A	7'	6'	5'
550DST		16"	22.0	N/A	60'	55'	48'	N/A	9'	8'	7'
520TST	Trussed Triple Track	10"	19.5	N/A	N/A	46'	38'	N/A	N/A	9' 2"	7' 7"
520QST	Trussed Quad Track	10"	20.1	N/A	N/A	N/A	46'	N/A	N/A	N/A	9' 2"
*306 Alu-Track	Aluminum Single Track	6"	5.6	11' 6"	9' 6"	8'	6' 6"	2' 4"	1' 11"	1' 7"	1' 4"
*308 Alu-Track	Aluminum Single Track	8"	7.7	20'	17'	14'	11'	4'	3' 5"	2' 10"	2'
*R308 Alu-Track	Reinforced Aluminum Single Track	12-1/2"	12.1	30'	26'	22'	18'	6'	5'	4'	3'

*Anchor Trolley™ is not available for this track series.

**Depending on End-User requirements, Anchor Trolley FA525-AT or Stainless Steel Rotating Eyebolt Trolley 524RISS can be used.

NOTE: All maximum dimensions are based on 30-degree off-plum (off-center) loading. Maximum Support Centers and Overhangs shown are for reference only and depend on exact system dimensions. Typically, the Maximum Overhang should not exceed 20 percent of the minimum support center. For Maximum Overhangs greater than 20 percent of the minimum support center, contact a Rigid Lifelines Technical Sales Support Specialist.



Form Number: RLL-TPF0301V2